



QE50LP-S-MB-QED-D0

Pyroelectric detector for laser energy measurement up to 85 J.



PRODUCT FAMILY KEY FEATURES

MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

LOW NOISE LEVEL

10 μ J for the MB coating

QED ATTENUATOR AVAILABLE

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. [Read more.](#)

HIGH REPETITION RATE OPTIONS

- QE-MB: 200 Hz (standard)
- QE-MB: 500 Hz (upon request)
- QE-MT: 4 000 Hz (standard)

TEST TARGET INCLUDED

With the MB models

SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

[STAND-D-233](#)

SPECIFICATIONS

MEASUREMENT CAPABILITIES

Spectral range ¹	0,3 - 2,1 μ m
Typical rise time	900 μ s
Repeatability	<0.5%
Maximum repetition frequency	200 Hz
Maximum measurable energy ²	85 J
Noise equivalent energy ³	20 μ J
Maximum pulse width	675 μ s
Energy calibration uncertainty	\pm 3 %

1. For the calibrated spectral range, see the user manual.
2. At 1064 nm, 7 ns, 10 Hz. Increasing pulse width increases maximum measurable energy.
3. Nominal value. Actual value depends on electrical noise in the measurement system.

DAMAGE THRESHOLDS

Maximum average power density ¹	600 W/cm ²
Maximum energy density ²	8 J/cm ²
Maximum power	25 W

1. May vary with wavelength and average power.
2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

PHYSICAL CHARACTERISTICS

Cooling	Convection
Aperture width	47 mm
Aperture height	47 mm
Absorber	QED
Dimensions	78H x 80W x 20D mm



Weight

0.21 kg

ORDERING INFORMATION

QE50LP-S-MB-QED-D0	202186
QE50LP-S-MB-QED-INE-D0	
QE50LP-S-MB-QED-INT-D0	202752
QE50LP-S-MB-QED-IDR-D0	203282

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us